

ECLASS-14.0	27242611
ETIM-5.0	EC001600
ETIM-6.0	EC001600
ETIM-7.0	EC001600
ETIM-8.0	EC001600
customs tariff number	85369010
EAN	4048879422864
Packaging unit	1

Electrical data | Supply

Operating voltage DC max.	0 V
Total current max.	10 A

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
-------------------------------------	------

Mechanical data | Mounting data

Height	109 mm
Width	12,9 mm
Depth	52,5 mm
Mounting method	geschnappt
Suitable for mounting type	(EN 60715), mounting rail

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	60 °C
Ambient temperature (storage, transport)	-25 °C

Connection type 2

Connection type 1	Power
Connection type 2	Power
Family construction form	terminal
No. of poles	8
Gender	female
Connection	Spring clamp terminals FK
PIN 1	n.c.
PIN 2	24 V DC
PIN 3	0 V
PIN 4	24 V DC Sys
PIN 5	n.c.
PIN 6	24 V DC
PIN 7	0 V
PIN 8	0 V Sys
Family construction form	terminal
No. of poles	8
Gender	female
Connection	Spring clamp terminals FK
PIN 1	0 V DC
PIN 2	0 V DC
PIN 3	0 V DC
PIN 4	0 V DC
PIN 5	0 V DC
PIN 6	0 V DC
PIN 7	0 V DC
PIN 8	0 V DC