

EUROCARD HOLDER

SKPD form D, 230V, 32-pole, 234x160mm

screw terminal  
32-pole  
230 V AC

To insert the card first press down the 2 yellow buttons. Then slide the Eurocard into the guide slots pushing until fully engaged. The card is now locked into position. It can be removed by pressing down on the 2 yellow buttons.

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27260710
ECLASS-6.1	27260704
ECLASS-7.0	27440402
ECLASS-8.0	27440402
ECLASS-9.0	27440402
ECLASS-10.1	27440402
ECLASS-11.1	27460201
ECLASS-12.0	27460201
ETIM-5.0	EC002780
customs tariff number	85366990
GTIN	4048879040051
Packaging unit	1
Electrical data   Supply	
Operating voltage AC	230 V
Operating current max.	4 A
Installation	
Connection cross-section solid min.	0,25 mm²
Connection cross-section solid max.	4 mm²
Connection cross-section stranded/fine-stranded min.	0,5 mm²

Connection cross-section stranded/fine-stranded max. 2,5 mm²

**Installation | Connection**

Connection Screw terminals SK

**Installation | Pin assignment**

No. of poles 32

**Device protection | Media**

Flame resistance flame retardant

**Mechanical data | Material data**

Material housing Plastic

**Mechanical data | Mounting data**

Mounting method screwed

Suitable for mounting type mounting rail

Height 63 mm

Width 274 mm

Depth 167 mm