

SCREW PLUG M12 STAINLESS STEEL

6-edges, 14 mm

Art.No.: 996076

Weight: 0.011

Country of origin: DE

Model designation: M12 MALE STAINLESS STEEL CAP -S02

Screw plug M12×1 mm

Metal, hex, 1 piece

Stainless steel 1.4305 (V2A)

[Link to Product](#)

Illustration



Product may differ from Image

Commercial data

ECLASS-6.0	23111190
ECLASS-6.1	23111190
ECLASS-7.0	23111190
ECLASS-8.0	23111190
ECLASS-9.0	23111102
ECLASS-10.1	23111190
ECLASS-11.1	23111102
ECLASS-12.0	23111102
ETIM-5.0	EC000032
customs tariff number	73269098
customs tariff number	73269098
GTIN	4048879333764
GTIN	4048879333764
Packaging unit	1
Packaging unit	1

Installation | Connection

Tightening torque	0,6 Nm
Mounting set	M12 x 1

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65, IP67, IP68
Degree of protection (ISO 20653:2013)	IP66K, IP69K
Additional condition protection degree	inserted, screwed

Material housing	Stainless steel 1.4305 (V2A)
------------------	------------------------------

Mounting method	inserted, screwed, Shaking protection
-----------------	---------------------------------------

Operating temperature min. -100 °C

Operating temperature max.	205 °C
----------------------------	--------