

MODLINK MSDD DATA INSERT

2xSUB-D9 female/male  
Art.No.: 4000-68000-0200000  
Weight: 0.04  
Country of origin: DE  
Model designation: FR.MODUL 2x9pol. Bu/St

SUB-D9; SUB-D9  
2× SUB-D9 (female/male)

Link to Product

Illustration



Product may differ from Image



Header

Material short textFR.MODUL 2x9pol. Bu/St

Commercial data

URL Webshop	https://shop.murrelektronik.com/4000-68000-0200000
GTIN	4048879038102
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806
ECLASS-14.0	27182806

ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85366990
EAN	4048879038102
Packaging unit	1

**Mechanical data | Mounting data**

Height	88 mm
Width	51 mm
Depth	40 mm

**Environmental characteristics | Climatic**

Storage temperature min.	-30 °C
Storage temperature max.	60 °C

**SUB-D9**

Family construction form	SUB-D9
Gender	female
No. of poles	9
Looking techniques	Standard UNC 4-40 screw thread bolt (EN 60807)
Family type Back side	SUB-D9
Gender Rear	male
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating current	3 A
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42.4 V
Current operating max. (UL)	175 mA