

MODLINK MSDD DATA INSERT

1xSUB-D9 female/female

Art.No.: 4000-68000-0240000

Weight: 0.027 kg

Country of origin: DE

Model designation: FR.MODUL 9 pol.Bu/Bu (Pin1 unten)

SUB-D9

1 x SUB-D9 (female/female)

Link to Product**Illustration**

Product may differ from Image

**Commercial data**

| | |
|---------------|---|
| URL Webshop | https://shop.murrelektronik.com/4000-68000-0240000 |
| GTIN | 4048879038065 |
| ECLASS-6.0 | 27189217 |
| ECLASS-6.1 | 27189217 |
| ECLASS-7.0 | 27189217 |
| ECLASS-7.1 | 27189217 |
| ECLASS-8.0 | 27189217 |
| ECLASS-8.1 | 27189217 |
| ECLASS-9.0 | 27182806 |
| ECLASS-9.1 | 27189217 |
| ECLASS-10.0.1 | 27182806 |
| ECLASS-10.1 | 27182806 |
| ECLASS-11.0 | 27182806 |
| ECLASS-11.1 | 27182806 |
| ECLASS-12.0 | 27182806 |
| ECLASS-13.0 | 27182806 |
| ECLASS-14.0 | 27182806 |
| ETIM-5.0 | EC002625 |
| ETIM-6.0 | EC002625 |

| | |
|-----------------------|---------------|
| ETIM-7.0 | EC002625 |
| ETIM-8.0 | EC002625 |
| customs tariff number | 85366990 |
| EAN | 4048879038065 |
| Packaging unit | 1 |

Mechanical data | Mounting data

| | |
|--------|-------|
| Height | 88 mm |
| Width | 51 mm |
| Depth | 15 mm |

Environmental characteristics | Climatic

| | |
|--|------------------|
| Ambient temperature (storage, transport) | -30 °C ... 60 °C |
|--|------------------|

SUB-D9

| | |
|---------------------------------------|--|
| Family construction form | SUB-D9 |
| Gender | female |
| No. of poles | 9 |
| Looking techniques | Standard UNC 4-40 screw thread bolt (EN 60807) |
| Family type Back side | SUB-D9 |
| Gender Rear | female |
| Operating voltage AC | 48 V |
| Operating voltage DC | 48 V |
| Operating current | 3 A |
| Operating voltage AC max. (UL-listed) | 30 V |
| Operating voltage DC max. (UL-listed) | 42,4 V |
| Current operating max. (UL) | 175 mA |