

MODLINK MSDD DATA INSERT

1×USB-A fem./fem.+1×RJ45 fem./fem.+1×DVI fem./fem.

Art.No.: 4000-68000-0820000
Weight: 0.06
Country of origin: TW
Model designation: FR.MODUL USB+RJ45+DVI

RJ45; USB (A); DVI
1× RJ45, 8-pole metal, CAT5e (female/female)
1× USB 2.0 (female/female) form A
1× DVI (female/female)

Link to Product

Illustration



Product may differ from Image



Commercial data	
URL Webshop	https://shop.murrelektronik.com/4000-68000-0820000
GTIN	4048879037853
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806
ECLASS-14.0	27182806

ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
EAN	4048879037853

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	45 mm

Environmental characteristics | Climatic

Storage temperature min.	-10 °C
Storage temperature max.	60 °C

USB

USB specification	2.0
Looking techniques	Snap-in connector
Data transmission rate max.	480 MBit/s
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating voltage DC (UL-listed)	42.4 V

RJ45

Family construction form	RJ45
Looking techniques	Snap-in connector
Cable category min.	Cat5e
Family type Back side	RJ45
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42.4 V
Current operating max. (UL)	175 mA

DVI

Gender	female
Family type Back side	DVI
Gender Rear	female
Operating voltage AC max.	40 V
Operating current max.	1.5 A