

MODLINK MSDD DATA INSERT

2×RJ45
Art.No.: 4000-68000-1200000
Weight: 0.067
Country of origin: DE
Model designation: FR.MODUL 2 x RJ45/45 geschirmt

RJ45; RJ45
2× RJ45, 8-pole metal, CAT5e (female/female)

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85366990
customs tariff number	85366990
GTIN	4048879037624
GTIN	4048879037624
Packaging unit	1
Packaging unit	1
Mechanical data Mounting data	

Height	88 mm
Width	51 mm
Depth	21 mm
Environmental characteristics Climatic	
Storage temperature min.	-10 °C
Storage temperature max.	60 °C
Shielding plate	
Connection information	Threaded hole M4
Tightening torque	0,9 Nm
RJ45	
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA
Family construction form	RJ45
Family type Back side	RJ45
Cable category min.	Cat5e
Looking techniques	Snap-in connector