

MODLINK MSDD DATA INSERT

1xUSB-A female/female + 1xRJ45

Art.No.: 4000-68000-1310000

Weight: 0.05

Country of origin: CZ

Model designation: Fr.Modul RJ45/45 + USB-geschirmt

USB (form A); RJ45

1× USB 3.0 (female/female) form A

1× RJ45, 8-pole metal, CAT5e (female/female)

Link to Product

Illustration



Product may differ from Image



| Commercial data | |
|-----------------|---|
| URL Webshop | https://shop.murrelektronik.com/4000-68000-1310000 |
| GTIN | 4048879037587 |
| ECLASS-6.0 | 27189217 |
| ECLASS-6.1 | 27189217 |
| ECLASS-7.0 | 27189217 |
| ECLASS-7.1 | 27189217 |
| ECLASS-8.0 | 27189217 |
| ECLASS-8.1 | 27189217 |
| ECLASS-9.0 | 27182806 |
| ECLASS-9.1 | 27189217 |
| ECLASS-10.0.1 | 27182806 |
| ECLASS-10.1 | 27182806 |
| ECLASS-11.0 | 27182806 |
| ECLASS-11.1 | 27182806 |
| ECLASS-12.0 | 27182806 |
| ECLASS-13.0 | 27182806 |
| ECLASS-14.0 | 27182806 |
| ETIM-5.0 | EC002625 |
| ETIM-6.0 | EC002625 |

| | |
|----------|---------------|
| ETIM-7.0 | EC002625 |
| ETIM-8.0 | EC002625 |
| EAN | 4048879037587 |

Mechanical data | Mounting data

| | |
|--------|---------|
| Height | 88 mm |
| Width | 51 mm |
| Depth | 70.4 mm |

Environmental characteristics | Climatic

| | |
|--------------------------|-------|
| Storage temperature min. | 5 °C |
| Storage temperature max. | 40 °C |

Shielding plate

| | |
|-----------------------------|------------------|
| Connection information | Threaded hole M4 |
| Tightening torque | 0.9 Nm |
| Tightening torque tolerance | ± 0.1 Nm |

USB

| | |
|---------------------------------------|-------------------|
| USB specification | 3.0 |
| Looking techniques | Snap-in connector |
| Data transmission rate max. | 5,000 MBit/s |
| Operating voltage AC | 48 V |
| Operating voltage DC | 48 V |
| Operating current | 1.5 A |
| Operating voltage AC max. (UL-listed) | 30 V |
| Operating voltage DC max. (UL-listed) | 42.4 V |

RJ45

| | |
|---------------------------------------|-------------------|
| Family construction form | RJ45 |
| Looking techniques | Snap-in connector |
| Cable category min. | Cat5e |
| Family type Back side | RJ45 |
| Operating voltage AC max. (UL-listed) | 30 V |
| Operating voltage DC max. (UL-listed) | 42.4 V |
| Current operating max. (UL) | 175 mA |