

MODLINK MSDD SOCKET INSERT USA NEMA 5-20

GFCI 125VAC/20A

Art.No.: 4000-68000-3280000  
Weight: 0.124  
Country of origin: CN  
Model designation: Fr.Modul-AB-125-20-GFCI-SC

USA (2× NEMA-GFCI 5-20)  
(Ground Fault Circuit Interrupter)  
Screw terminals

Link to Product

Illustration



Product may differ from Image



Commercial data	
URL Webshop	https://shop.murrelektronik.com/4000-68000-3280000
GTIN	4048879037259
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806
ECLASS-14.0	27182806
ETIM-5.0	EC000020
ETIM-6.0	EC000020

ETIM-7.0	EC000020
ETIM-8.0	EC000020
EAN	4048879037259

**Mechanical data | Mounting data**

Height	88 mm
Width	51 mm
Depth	27 mm

**Environmental characteristics | Climatic**

Storage temperature min.	-30 °C
Storage temperature max.	60 °C

**USA**

Connection	Screw terminals SK
No. of poles	PE
Connections per pole	2
Protection contact present	yes
Connection cross section max.	6 mm <sup>2</sup>
AWG number max.	10
Operating voltage AC	125 V
Operating current	20 A