

MODLINK MSDD SINGLE COMBI INSERT USA NEMA 5-15

2xRJ45 female/female

Art.No.: 4000-68000-4060000
Weight: 0.044
Country of origin: DE
Model designation: Fr.Modul-AB-125-15-SO+2xRJ45

1 × NEMA 1-15 (plug-solder connection)
2 × RJ45, 8-pole metal, CAT5e (female/female)

Link to Product

Illustration



Product may differ from Image



Commercial data	
URL Webshop	https://shop.murrelektronik.com/4000-68000-4060000
GTIN	4048879371483
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806
ECLASS-14.0	27182806
ETIM-5.0	EC000020
ETIM-6.0	EC000020

ETIM-7.0	EC000020
ETIM-8.0	EC000020
EAN	4048879371483

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	25 mm

Environmental characteristics | Climatic

Storage temperature min.	5 °C
Storage temperature max.	40 °C

USA

Connection	Plug-solder connection
No. of poles	PE
Protection contact present	yes
Operating voltage AC	125 V
Operating current	15 A

RJ45

Family construction form	RJ45
Looking techniques	Snap-in connector
Cable category min.	Cat5e
Family type Back side	RJ45
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42.4 V
Current operating max. (UL)	175 mA