

**MODLINK MSDD SINGLE COMBI INSERT USA NEMA 5-15**

2xRJ45 female/female

Art.No.: 4000-68000-4060000

Weight: 0.044 kg

Country of origin: DE

Model designation: Fr.Modul-AB-125-15-SO+2xRJ45

1 × NEMA 1-15 (plug-solder connection)

2 × RJ45, 8-pole metal, CAT5e (female/female)

**Link to Product****Illustration**

Product may differ from Image

**Commercial data**

URL Webshop	<a href="https://shop.murrelektronik.com/4000-68000-4060000">https://shop.murrelektronik.com/4000-68000-4060000</a>
GTIN	4048879371483
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806
ECLASS-14.0	27182806
ETIM-5.0	EC000020
ETIM-6.0	EC000020

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-05-05

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

ETIM-7.0	EC000020
ETIM-8.0	EC000020
customs tariff number	85366990
EAN	4048879371483
Packaging unit	1

#### Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	25 mm

#### Environmental characteristics | Climatic

Ambient temperature (storage, transport)	5 °C ... 40 °C
--	----------------

#### USA

Connection	Plug-solder connection
No. of poles	2 + PE
Protection contact present	Yes
Operating voltage AC	125 V
Operating current	15 A

#### RJ45

Family construction form	RJ45
Looking techniques	Snap-in connector
Cable category min.	Cat5e
Family type Back side	RJ45
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA