

**MODLINK MSDD SINGLE COMBI INSERT USA NEMA 5-15**

2xRJ45 female/female

1 × NEMA 1-15 (plug-solder connection)

2 × RJ45, 8-pole metal, CAT5e (female/female)

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC000020
customs tariff number	85366990
GTIN	4048879371483
Packaging unit	1

**Mechanical data | Mounting data**

Height	88 mm
Width	51 mm
Depth	25 mm

**Environmental characteristics | Climatic**

Storage temperature min.	5 °C
Storage temperature max.	40 °C

**USA**

Connection geometry	4.8 x 0.5 mm
---------------------	--------------

Operating voltage AC	125 V
Operating current	15 A
Connection	Plug-solder connection
No. of poles	2 + PE
Protection contact present	yes
<b>RJ45</b>	
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA
Family construction form	RJ45
Family type Back side	RJ45
Cable category min.	Cat5e
Looking techniques	Snap-in connector