

MODLINK MSDD SINGLE COMBI INSERT INDIA

1x RJ45 + 1x data cutout  
Art.No.: 4000-68000-4570001  
Weight: 0.077  
Country of origin: DE  
Model designation: Fr.Modul-D-250-5-SC+RJ45+1xdata cutout  
  
1 x India (white)  
1 x RJ45, 8-pole metal, CAT6A (female/female)  
1 x RJ45 cut-out

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85366990
customs tariff number	85366990
GTIN	4048879601115
GTIN	4048879601115
Packaging unit	1
Packaging unit	1
Device protection   Electrical	

Degree of protection (EN IEC 60529) IP20

#### Mechanical data | Mounting data

Height	87,5 mm
Width	50,7 mm
Depth	30,7 mm

#### Environmental characteristics | Climatic

Operating temperature min.	-5 °C
Operating temperature max.	50 °C
Storage temperature min.	-10 °C
Storage temperature max.	60 °C

#### Shielding plate

Connection information	Threaded hole M4
Tightening torque	0,9 Nm

#### India

Connection cross section max.	1,5 mm <sup>2</sup>
AWG number max.	16
Operating voltage AC	240 V
Operating current	5 A
Connection	Screw terminals SK
No. of poles	2 + PE
Connections per pole	2
Protection contact present	yes

#### RJ45

Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA
Family construction form	RJ45
Family type Back side	RJ45
Cable category min.	Cat6a
Looking techniques	Snap-in connector