

SIGNAL TOWER MODLIGHT30 EQUIPPED WITH LED MODULES

Green,amber,red with 4 pole M12 connection

Art.No.: 4000-75330-5310000

Weight: 0.135 kg

Country of origin: ID

Model designation: Modlight30-B-70 M12 mit LED GYR

Connection module + LED modules

green, yellow, red
with M12 connection

Connection cables are in the online shop under "Connection Technology".

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data

URL Webshop	https://shop.murrelektronik.com/4000-75330-5310000
GTIN	4048879496896
Customs tariff number	85318070
ECLASS-6.0	27371230
ECLASS-6.1	27371230
ECLASS-7.0	27371230
ECLASS-7.1	27371230
ECLASS-8.0	27371230
ECLASS-8.1	27371230
ECLASS-9.0	27371230
ECLASS-9.1	27371230
ECLASS-10.0.1	27371230
ECLASS-10.1	27371230
ECLASS-11.0	27371230
ECLASS-11.1	27371230
ECLASS-12.0	27371230
ECLASS-13.0	27371230
ECLASS-14.0	27371230

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2026-05-02

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

ETIM-5.0	EC001042
ETIM-6.0	EC001042
ETIM-7.0	EC001042
ETIM-8.0	EC001042
customs tariff number	85318070
EAN	4048879496896
Packaging unit	1

Electrical data | Supply

Operating voltage AC	24 V
Operating voltage DC	24 V
Current consumption max.	85 mA

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
-------------------------------------	------

Mechanical data | Material data

housing	Plastic
Color housing	black

Mechanical data | Mounting data

Height	30 mm
Width	30 mm
Depth	213 mm

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	60 °C

Connection type 1

Family construction form	M12
No. of poles	4
Coding	A
Gender	male
PIN 1	GN
PIN 2	RD
PIN 3	COM
PIN 4	YE