

**COMLIGHT56 LED STATUS LIGHT**

Multicolor, IO-Link

Art.No.: 4000-76056-0000001

Weight: 0.090 kg

Country of origin: ID

Model designation: Comlight56 M12-4U-IOL

**Link to Product****Illustration**

Product may differ from Image

**Commercial data**

URL Webshop	<a href="https://shop.murrelektronik.com/4000-76056-0000001">https://shop.murrelektronik.com/4000-76056-0000001</a>
GTIN	4048879868433
Customs tariff number	85319000
ECLASS-6.0	27371220
ECLASS-6.1	27110390
ECLASS-7.0	27110390
ECLASS-7.1	27110390
ECLASS-8.0	27110390
ECLASS-8.1	27110390
ECLASS-9.0	27110350
ECLASS-9.1	27110345
ECLASS-10.0.1	27110345
ECLASS-10.1	27110350
ECLASS-11.0	27110345
ECLASS-11.1	27110350
ECLASS-12.0	27110350
ECLASS-13.0	27110345
ECLASS-14.0	27110345
ETIM-5.0	EC000232
ETIM-6.0	EC000232
ETIM-7.0	EC000232

ETIM-8.0	EC000232
customs tariff number	85319000
EAN	4048879868433
Packaging unit	1
<b>Electrical data   Supply</b>	
Operating voltage DC	24 V
Operating voltage DC min.	18 V
Operating voltage DC max.	30 V
Nominal current	40 mA
Nominal rating	1 W
<b>Industrial communication   IO-Link</b>	
type	Device
Port Class	A
revision ID	V1.1
transmission rate	COM2 (38.4 kbit/s)
process data length input	1 bytes
process data length output	2 bytes
cycle time min.	8 ms
<b>Device protection   Electrical</b>	
Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	locked, inserted
<b>Mechanical data   Material data</b>	
housing	PC
<b>Mechanical data   Mounting data</b>	
Height	97,2 mm
Width	56 mm
Depth	56 mm
<b>Environmental characteristics   Climatic</b>	
Operating temperature min.	-25 °C
Operating temperature max.	60 °C
Ambient temperature (storage, transport)	-40 °C ... 75 °C
<b>Connection type 1</b>	
Family construction form	M12
No. of poles	4
Coding	A
Gender	male
PIN 1	BN 24 V DC (0 V)
PIN 3	BU 0 V (24 V DC)
PIN 4	BK IO-Link