

Signal tower Modlight50 Pro equipped with LED modules

green,amber,red,buzzer

Art.No.: 4000-76502-5310000  
Weight: 0.26  
Country of origin: ID  
Model designation: Modlight50 Pro BASE LED-GYR BUZZER

Basic, buzzer, flash + LED modules  
green, yellow, red

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27371230
ECLASS-6.1	27371230
ECLASS-7.0	27371230
ECLASS-8.0	27371230
ECLASS-9.0	27371230
ECLASS-10.1	27371230
ECLASS-11.1	27371230
ECLASS-12.0	27371230
ETIM-5.0	EC001042
ETIM-6.0	EC001042
ETIM-7.0	EC001042
ETIM-8.0	EC001042
customs tariff number	85318070
customs tariff number	85318070
EAN	4048879759656
EAN	4048879759656
Packaging unit	1
Packaging unit	1
Electrical data   Supply	

Operating voltage DC	24 V
Operating voltage DC min.	21,6 V
Operating voltage DC max.	26,4 V
Current consumption max.	385 mA
<b>Industrial communication   HMI</b>	
Reduced sound pressure at 1 m	80 dB
Sound pressure at 1 m	90 dB
<b>HMI   Illumination properties</b>	
Blink cycles	60 ±12 per minute
<b>Device protection   Electrical</b>	
Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked
<b>Mechanical data   Material data</b>	
Material housing	Plastic
Color housing	black
<b>Mechanical data   Mounting data</b>	
Height	253,5 mm
Width	50 mm
Depth	50 mm
<b>Environmental characteristics   Climatic</b>	
Operating temperature min.	-30 °C
Operating temperature max.	60 °C