

Signal tower Modlight50 Pro equipped with LED modules

blue,green,amber,red,buzzer

Art.No.: 4000-76502-6531000  
Weight: 0.3  
Country of origin: ID  
Model designation: Modlight50 Pro BASE LED-BGYR BUZZER

red, yellow, green, blue

Link to Product

Illustration



Product may differ from Image



Header

Material short textModlight50 Pro BASE LED-BGYR BUZZER

Commercial data

URL Webshop	https://shop.murrelektronik.com/4000-76502-6531000
GTIN	4048879759649
ECLASS-6.0	27371230
ECLASS-6.1	27371230
ECLASS-7.0	27371230
ECLASS-7.1	27371230
ECLASS-8.0	27371230
ECLASS-8.1	27371230
ECLASS-9.0	27371230
ECLASS-9.1	27371230
ECLASS-10.0.1	27371230
ECLASS-10.1	27371230
ECLASS-11.0	27371230
ECLASS-11.1	27371230
ECLASS-12.0	27371230
ECLASS-13.0	27371230
ECLASS-14.0	27371230
ETIM-5.0	EC001042

ETIM-6.0	EC001042
ETIM-7.0	EC001042
ETIM-8.0	EC001042
customs tariff number	85318070
EAN	4048879759649
Packaging unit	1

**Electrical data | Supply**

Operating voltage DC	24 V
Operating voltage DC min.	21.6 V
Operating voltage DC max.	26.4 V
Current consumption max.	430 mA

**Device protection | Electrical**

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	locked, inserted

**Mechanical data | Material data**

Material housing	Plastic
Color housing	black

**Mechanical data | Mounting data**

Height	293.5 mm
Width	50 mm
Depth	50 mm

**Environmental characteristics | Climatic**

Operating temperature min.	-30 °C
Operating temperature max.	60 °C