

Signal tower Modlight70 Pro equipped with LED modules

white,blue,green ,red and buzzer, M12 plug downward

Art.No.: 4000-76705-7651900

Weight: 0.530 kg

Country of origin: ID

Model designation: Modlight70 Pro BASE M12-8U LED-WBGR BUZ.

Link to Product

Illustration



Product may differ from Image



Commercial data

URL Webshop	https://shop.murrelektronik.com/4000-76705-7651900
GTIN	4048879825382
Customs tariff number	85318070
ECLASS-6.0	27371230
ECLASS-6.1	27371230
ECLASS-7.0	27371230
ECLASS-7.1	27371230
ECLASS-8.0	27371230
ECLASS-8.1	27371230
ECLASS-9.0	27371230
ECLASS-9.1	27371230
ECLASS-10.0.1	27371230
ECLASS-10.1	27371230
ECLASS-11.0	27371230
ECLASS-11.1	27371230
ECLASS-12.0	27371230
ECLASS-13.0	27371230
ECLASS-14.0	27371230
ETIM-5.0	EC001042
ETIM-6.0	EC001042
ETIM-7.0	EC001042

ETIM-8.0	EC001042
customs tariff number	85318070
EAN	4048879825382
Packaging unit	1

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	21,6 V
Operating voltage DC max.	26,4 V
Current consumption max.	430 mA

Mechanical data | Material data

housing	Plastic
Color housing	black

Mechanical data | Mounting data

Height	334 mm
Width	70 mm
Depth	70 mm

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	50 °C
Ambient temperature (storage, transport)	-30 °C ... 60 °C

Connection type 1

Family construction form	M12
No. of poles	8
Coding	A
Gender	male
PIN 1	24 V DC (0 V)
PIN 2	LED-Modul RD
PIN 3	0 V (24 V DC)
PIN 4	LED-Modul CL
PIN 5	LED-Modul YE
PIN 6	LED-Modul BU
PIN 7	LED-Modul GN
PIN 8	-