

## Signal tower Modlight70 Pro equipped with LED modules

white,blue,green ,red and buzzer, M12 plug downward

Art.No.: 4000-76705-7651900

Weight: 0.53

Country of origin: ID

Model designation: Modlight70 Pro BASE M12-8U LED-WBGR BUZ.

### [Link to Product](#)

#### Illustration



Product may differ from Image



#### Commercial data

ECLASS-6.0	27371230
ECLASS-6.1	27371230
ECLASS-7.0	27371230
ECLASS-8.0	27371230
ECLASS-9.0	27371230
ECLASS-10.1	27371230
ECLASS-11.1	27371230
ECLASS-12.0	27371230
ETIM-5.0	EC001042
customs tariff number	85318070
customs tariff number	85318070
GTIN	4048879825382
GTIN	4048879825382
Packaging unit	1
Packaging unit	1

#### Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	21,6 V
Operating voltage DC max.	26,4 V
Current consumption max.	430 mA

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-04-27

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

**Mechanical data | Material data**

Material housing	Plastic
Color housing	black

**Mechanical data | Mounting data**

Height	334 mm
Width	70 mm
Depth	70 mm

**Environmental characteristics | Climatic**

Operating temperature min.	-20 °C
Operating temperature max.	50 °C
Storage temperature min.	-30 °C
Storage temperature max.	60 °C

**Connection type 1**

Family construction form	M12
Gender	male
Coding	A
No. of poles	8
PIN 1	24 V DC (0 V)
PIN 2	LED-Modul RD
PIN 3	0 V (24 V DC)
PIN 4	LED-Modul CL
PIN 5	LED-Modul YE
PIN 6	LED-Modul BU
PIN 7	LED-Modul GN
PIN 8	-