

1,6 mm crimp contact f/turned/gold/0,75-1 mm²

100 pieces

Art.No.: 70MH-ZKB1G-0100300

Weight: 0.001

Country of origin: CZ

Model designation: MSMH-ZK-BU gedreht/g-1,6mm 0,75-1mm²

Turned crimp contact

Female

1.6 mm

0.75...1 mm² (AWG 18)

Quantity: 100 pcs.

Technical data will be only guaranteed with Murrelektronik components.

[Link to Product](#)**Illustration**

Product may differ from Image

Commercial data

ECLASS-6.0	27143424
ECLASS-6.1	27261202
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796
customs tariff number	85366990
customs tariff number	85366990
GTIN	4048879653589
GTIN	4048879653589
Packaging unit	100
Packaging unit	100

Installation

Connection cross section min.	0,75 mm ²
Connection cross section max.	1 mm ²
AWG number max.	18

Installation | Connection

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-05-11

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

Stripping length	7 mm
Connection	Crimp
Gender	female
Mating cycles min.	500

Mechanical data | Material data

Coating contact	gold plated
Material contact	Brass

Mechanical data | Mounting data

Height	3,5 mm
Width	3,5 mm
Depth	21,6 mm