

2,5 mm crimp contact f/turned/gold/1,5 mm²

100 pieces

Art.No.: 70MH-ZKB1G-0200400

Weight: 0.002

Country of origin: CZ

Model designation: MSMH-ZK-BU gedreht/g-2,5mm 1,5mm²

Turned crimp contact

Female

2.5 mm

1.5 mm² (AWG 16)

Quantity: 100 pcs.

Technical data will be only guaranteed with Murrelektronik components.

[Link to Product](#)**Illustration**

Product may differ from Image

Commercial data

ECLASS-6.0	27143424
ECLASS-6.1	27261202
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796
customs tariff number	85366990
customs tariff number	85366990
GTIN	4048879653688
GTIN	4048879653688
Packaging unit	100
Packaging unit	100

Installation

Connection cross section max.	1,5 mm ²
AWG number max.	16

Installation | Connection

Stripping length	6,5 mm
------------------	--------

Connection	Crimp
Gender	female
Mating cycles min.	500
Mechanical data Material data	
Coating contact	gold plated
Material contact	Brass
Mechanical data Mounting data	
Height	4,5 mm
Width	4,5 mm
Depth	22 mm