

2,5 mm crimp contact f/turned/gold/2,5 mm²

100 pieces

Art.No.: 70MH-ZKB1G-0200500

Weight: 0.002

Country of origin: CZ

Model designation: MSMH-ZK-BU gedreht/g-2,5mm 2,5mm²

Turned crimp contact

Female

2.5 mm

2.5 mm² (AWG 14)

Quantity: 100 pcs.

Technical data will be only guaranteed with Murrelektronik components.

[Link to Product](#)**Illustration**

Product may differ from Image

Commercial data

ECLASS-6.0	27143424
ECLASS-6.1	27261202
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796
customs tariff number	85366990
customs tariff number	85366990
GTIN	4048879653695
GTIN	4048879653695
Packaging unit	100
Packaging unit	100

Installation

Connection cross section max.	2,5 mm ²
AWG number max.	14

Installation | Connection

Stripping length	6,5 mm
------------------	--------

Connection	Crimp
Gender	female
Mating cycles min.	500

Mechanical data | Material data

Coating contact	gold plated
Material contact	Brass

Mechanical data | Mounting data

Height	4,5 mm
Width	4,5 mm
Depth	22 mm