

1,6 mm crimp contact f/turned/silver/0,5 mm²

100 pieces

Art.No.: 70MH-ZKB1S-0100200

Weight: 0.001

Country of origin: CZ

Model designation: MSMH-ZK-BU gedreht/s-1,6mm 0,5mm²

Turned crimp contact

Female

1.6 mm

0.5 mm² (AWG 20)

Quantity: 100 pcs.

Technical data will be only guaranteed with Murrelektronik components.

[Link to Product](#)**Illustration**

Product may differ from Image

Commercial data

ECLASS-6.0	27143424
ECLASS-6.1	27261202
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796
customs tariff number	85366990
customs tariff number	85366990
GTIN	4048879653510
GTIN	4048879653510
Packaging unit	100
Packaging unit	100

Installation

Connection cross section max.	0,5 mm ²
AWG number max.	20

Installation | Connection

Stripping length	7 mm
------------------	------

Connection	Crimp
Gender	female
Mating cycles min.	500
Mechanical data Material data	
Coating contact	silver-plated
Material contact	Brass
Mechanical data Mounting data	
Height	3,5 mm
Width	3,5 mm
Depth	21,6 mm