

4 mm crimp contact f/turned/silver/4 mm²

100 pieces

Art.No.: 70MH-ZKB1S-0300600  
Weight: 0.003  
Country of origin: CZ  
Model designation: MSMH-ZK-BU gedreht/s-4,0mm 4mm²

Turned crimp contact  
Female  
4 mm  
4 mm² (AWG 12)  
Quantity: 100 pcs.  
Technical data will be only guaranteed with Murrelektronik components.

Link to Product

Illustration



Product may differ from Image

Commercial data	
ECLASS-6.0	27143424
ECLASS-6.1	27261202
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796
customs tariff number	85366990
customs tariff number	85366990
GTIN	4048879653787
GTIN	4048879653787
Packaging unit	100
Packaging unit	100
Installation	
Connection cross section max.	4 mm²
AWG number max.	12
Installation   Connection	
Stripping length	9 mm

Connection	Crimp
Gender	female
Mating cycles min.	500

**Mechanical data | Material data**

Coating contact	silver-plated
Material contact	Brass

**Mechanical data | Mounting data**

Height	6 mm
Width	6 mm
Depth	23,3 mm