

**4 mm crimp contact f/turned/silver/6 mm<sup>2</sup>**

100 pieces

Art.No.: 70MH-ZKB1S-0300700

Weight: 0.003

Country of origin: CZ

Model designation: MSMH-ZK-BU gedreht/s-4,0mm 6mm<sup>2</sup>

Turned crimp contact

Female

4 mm

6 mm<sup>2</sup> (AWG 10)

Quantity: 100 pcs.

Technical data will be only guaranteed with Murrelektronik components.

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	27143424
ECLASS-6.1	27261202
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796
customs tariff number	85366990
customs tariff number	85366990
GTIN	4048879653794
GTIN	4048879653794
Packaging unit	100
Packaging unit	100

**Installation**

Connection cross section max.	6 mm <sup>2</sup>
AWG number max.	10

**Installation | Connection**

Stripping length	9 mm
------------------	------

Connection	Crimp
Gender	female
Mating cycles min.	500
<b>Mechanical data   Material data</b>	
Coating contact	silver-plated
Material contact	Brass
<b>Mechanical data   Mounting data</b>	
Height	6 mm
Width	6 mm
Depth	23,3 mm