

**4 mm crimp contact f/turned/silver/10 mm<sup>2</sup>**

100 pieces

Art.No.: 70MH-ZKB1S-0300800

Weight: 0.003

Country of origin: CZ

Model designation: MSMH-ZK-BU gedreht/s-4,0mm 10mm<sup>2</sup>

Turned crimp contact

Female

4 mm

10 mm<sup>2</sup> (AWG 8)

Quantity: 100 pcs.

Technical data will be only guaranteed with Murrelektronik components.

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	27143424
ECLASS-6.1	27261202
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796
customs tariff number	85366990
customs tariff number	85366990
GTIN	4048879653800
GTIN	4048879653800
Packaging unit	100
Packaging unit	100

**Installation**

Connection cross section max.	10 mm <sup>2</sup>
AWG number max.	8

**Installation | Connection**

Stripping length	9 mm
------------------	------

Connection	Crimp
Gender	female
Mating cycles min.	500

**Mechanical data | Material data**

Coating contact	silver-plated
Material contact	Brass

**Mechanical data | Mounting data**

Height	6 mm
Width	6 mm
Depth	23,3 mm