

8 mm crimp contact f/turned/silver/25 mm²

2 pieces

Art.No.: 70MH-ZKB1S-0401000

Weight: 0.025

Country of origin: CZ

Model designation: MSMH-ZK-BU gedreht/s-8mm 25mm²

Turned crimp contact

Female

8 mm

25 mm² (AWG 4)

Quantity: 100 pcs.

Technical data will be only guaranteed with Murrelektronik components.

[Link to Product](#)**Illustration**

Product may differ from Image

Commercial data

ECLASS-6.0	27143424
ECLASS-6.1	27261202
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796
customs tariff number	85366990
customs tariff number	85366990
GTIN	4048879649728
GTIN	4048879649728
Packaging unit	2
Packaging unit	2

Installation

Connection cross section max.	25 mm ²
AWG number max.	4

Installation | Connection

Stripping length	16 mm
------------------	-------

Connection	Crimp
Gender	female
Mating cycles min.	500

Mechanical data | Material data

Coating contact	silver-plated
Material contact	Brass

Mechanical data | Mounting data

Height	13 mm
Width	13 mm
Depth	43 mm