

Coax insert 50Ohm (female)

Art.No.: 70MH-ZKF01-0000000
Weight: 0.033
Country of origin: CZ
Model designation: MSMH-ZK-BU-Einsatz-50Ohm

Coax insert
Female
1-pole
Technical data will be only guaranteed with Murrelektronik components.

Link to Product

Illustration



Product may differ from Image

Commercial data	
ECLASS-6.0	27143424
ECLASS-6.1	27261202
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000438
customs tariff number	85389099
customs tariff number	85389099
GTIN	4048879649483
GTIN	4048879649483
Packaging unit	1
Packaging unit	1
Electrical data	
Insertion loss max.	0,5 dB
Electrical data Supply	
Operating voltage AC	50 V
Operating voltage DC	50 V
Operating current	16 A
Industrial communication HMI	
Return loss min.	30 dB

Installation	
Connection cross section min.	0,14 mm ²
Connection cross section max.	2,5 mm ²
AWG number min.	26
AWG number max.	13
Installation Connection	
Wire insulation diameter min.	9,5 mm
Connection	Crimp
Gender	female
Mating cycles min.	500
Installation Pin assignment	
No. of poles	1
Device protection Electrical	
Pollution Degree	3
Rated surge voltage	0,8 kV
Insulation resistance min.	100 MΩ
Overvoltage category (EN 60664-1)	I
Overvoltage category (EN 60950-1)	III
Mechanical data Material data	
Material housing	PA
Combustibility class (UL94)	V-0
Mechanical data Mounting data	
Height	20,3 mm
Width	16,7 mm
Depth	45,6 mm
Environmental characteristics Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	125 °C
Climatic category (EN IEC 60068-1)	40/125/10