

EXACT12, 4XM12, 5-POLE, BASIC HOUSING, W.O. LED'S

Without homerun-cable

Art.No.: 8000-84502-0000000

Weight: 0.078 Country of origin: DE

Model designation: MVP12N-MK4F-XA

4-way, 5-pole

without LED, up to 125 V AC/DC

Screw plug-in terminals

Plastic housings with good resistance against chemicals and oils.


The resistance to aggressive media should be individually tested for your application. Further details on request.


Further cable lengths on request.


Link to Product

Illustration













stay connected





Product may differ from Image









Header	
Material short text	MVP12N-MK4F-XA
Commercial data	
URL Webshop	https://shop.murrelektronik.com/8000-84502-0000000
GTIN	4048879055833
ECLASS-6.0	27279219
ECLASS-6.1	27279219
ECLASS-7.0	27279219
ECLASS-7.1	27279219
ECLASS-8.0	27279219
ECLASS-8.1	27279219
ECLASS-9.0	27440111
ECLASS-10.0.1	27440111
ECLASS-10.1	27440111
ECLASS-11.0	27440111
ECLASS-11.1	27440111
ECLASS-12.0	27440111
ECLASS-13.0	27440111
ECLASS-14.0	27440111
ETIM-5.0	EC002585
ETIM-6.0	EC002585
ETIM-7.0	EC002585
ETIM-8.0	EC002585
customs tariff number	85366990
EAN	4048879055833
Packaging unit	1
Electrical data Supply	
Operating voltage AC	125 V
Operating voltage DC	125 V
Current operating per contact max.	4 A
Total current max.	8 A
Device protection Electrical	



Degree of protection (EN IEC 60529)	IP67, IP65	
Device protection Media		
Flame resistance	flame retardant	
Mechanical data Material data		
Material housing	Plastic	
Environmental characteristics Climatic		
Operating temperature min.	-20 °C	
Operating temperature max.	70 °C	
Connection type 2		
Family construction form	Сар	
No. of poles	16	
Family construction form	M12	
No. of poles	5	
Coding	A	
Gender	female	
Color contact carrier	black	
PIN 1	+	
PIN 2	NC S 2	
PIN 3	-	
PIN 4	NO S 1	
PIN 5	PE	