

**EXACT12, 8XM12, 4 POLE BASIC HOUSING, W.O. LED'S**

Without homerun-cable

Art.No.: 8000-88402-0000000

Weight: 0.125 kg

Country of origin: DE

Model designation: MVP12N-MK8V-XA

8-way, 4-pole




without LED, up to 125 V AC/DC



Screw plug-in terminals

Plastic housings with good resistance against chemicals and oils.


The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

[Link to Product](#)**Illustration**



Product may differ from Image



Header	
Material short text	MVP12N-MK8V-XA
Commercial data	
URL Webshop	<a href="https://shop.murrelektronik.com/8000-88402-0000000">https://shop.murrelektronik.com/8000-88402-0000000</a>
GTIN	4048879054287
ECLASS-6.0	27143423
ECLASS-6.1	27279219
ECLASS-7.0	27279219
ECLASS-7.1	27279219
ECLASS-8.0	27279219
ECLASS-8.1	27279219
ECLASS-9.0	27440111
ECLASS-10.0.1	27440111
ECLASS-10.1	27440111
ECLASS-11.0	27440111
ECLASS-11.1	27440111
ECLASS-12.0	27440111
ECLASS-13.0	27440111
ECLASS-14.0	27440111
ETIM-5.0	EC002585
ETIM-6.0	EC002585
ETIM-7.0	EC002585
ETIM-8.0	EC002585
customs tariff number	85366990
EAN	4048879054287
Packaging unit	1
Electrical data   Supply	
Operating voltage AC	125 V
Operating voltage DC	125 V
Current operating per contact max.	4 A
Total current max.	8 A
Device protection   Electrical	

Degree of protection (EN IEC 60529) IP67, IP65

#### Device protection | Media

Flame resistance flame retardant

#### Mechanical data | Material data

Material housing Plastic

#### Environmental characteristics | Climatic

Operating temperature min. -20 °C

Operating temperature max. 70 °C

#### Connection type 2

Family construction form Cap

No. of poles 14

Family construction form M12

No. of poles 4

Coding A

Gender female

Color contact carrier black

PIN 1 +

PIN 2 n.c.

PIN 3 -

PIN 4 NO S 1

PIN 5 PE