

EXACT12, 8XM12, 5-POLE, BASIC HOUSING

Without homerun-cable

Art.No.: 8000-88500-0000000

Weight: 0.133 kg

Country of origin: DE

Model designation: MVP12N-MN8F




8-way, 5-pole


Form PNP

Screw-plug-in terminals

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**



Product may differ from Image



Header	
Material short text	MVP12N-MN8F
Commercial data	
URL Webshop	https://shop.murrelektronik.com/8000-88500-0000000
GTIN	4048879054065
ECLASS-6.0	27143423
ECLASS-6.1	27279219
ECLASS-7.0	27279219
ECLASS-7.1	27279219
ECLASS-8.0	27279219
ECLASS-8.1	27279219
ECLASS-9.0	27440111
ECLASS-10.0.1	27440111
ECLASS-10.1	27440111
ECLASS-11.0	27440111
ECLASS-11.1	27440111
ECLASS-12.0	27440111
ECLASS-13.0	27440111
ECLASS-14.0	27440111
ETIM-5.0	EC002585
ETIM-6.0	EC002585
ETIM-7.0	EC002585
ETIM-8.0	EC002585
customs tariff number	85366990
EAN	4048879054065
Packaging unit	1
Electrical data Supply	
Operating voltage DC	24 V
Current operating per contact max.	4 A
Total current max.	8 A
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP67, IP65

Flame resistance flame retardant

Material housing	Plastic
------------------	---------

Operating temperature min. -20 °C

Operating temperature max.	70 °C
----------------------------	-------