

## **EXACT12, 8XM12, 5-POLE, BASIC HOUSING, NPN-LED'S**

Without homerun-cable

Art.No.: 8000-88501-0000000

Weight: 0.127

Country of origin: DE

Model designation: MVP12N-MK8F-NP

8-way, 5-pole Form NPN

Screw plug-in terminals


Plastic housings with good resistance against chemicals and oils.


The resistance to aggressive media should be individually tested for your application. Further details on request.


## **Link to Product**

## Illustration












stay connected



Product may differ from Image









Header	
Material short text	MVP12N-MK8F-NP
Commercial data	
URL Webshop	https://shop.murrelektronik.com/8000-88501-0000000
GTIN	4048879054058
ECLASS-6.0	27143423
ECLASS-6.1	27279219
ECLASS-7.0	27279219
ECLASS-7.1	27279219
ECLASS-8.0	27279219
ECLASS-8.1	27279219
ECLASS-9.0	27440111
ECLASS-10.0.1	27440111
ECLASS-10.1	27440111
ECLASS-11.0	27440111
ECLASS-11.1	27440111
ECLASS-12.0	27440111
ECLASS-13.0	27440111
ECLASS-14.0	27440111
ETIM-5.0	EC002585
ETIM-6.0	EC002585
ETIM-7.0	EC002585
ETIM-8.0	EC002585
customs tariff number	85366990
EAN	4048879054058
Packaging unit	1
Electrical data   Supply	
Operating voltage DC	24 V
Current operating per contact max.	4 A
Total current max.	8 A
Device protection   Electrical	
Degree of protection (EN IEC 60529)	IP67, IP65



Device protection   Media		
Flame resistance	flame retardant	
Mechanical data   Material data		
Material housing	Plastic	
Environmental characteristics   Climat	ic	
Operating temperature min.	-20 °C	
Operating temperature max.	70 °C	