

CAP BIG WITH PLUG. SPRING TERM. 21-POLE

For use with 4-,6-,8-way d-box M12 5-pole

Art.No.: 8000-88549-0000000

Weight: 0.048

Country of origin: CZ



Model designation: MVZ12-HFK21H MVMX 21P.

Cap for 4-, 6-, and 8-way distribution box, 5-pole

Spring clamp plug-in terminals

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

URL Webshop

<https://shop.murrelektronik.com/8000-88549-0000000>

GTIN

4048879300032

ECLASS-6.0	27143423
ECLASS-6.1	27279219
ECLASS-7.0	27279219
ECLASS-7.1	27279219
ECLASS-8.0	27279219
ECLASS-8.1	27279219
ECLASS-9.0	27440111
ECLASS-10.0.1	27440111
ECLASS-10.1	27440111
ECLASS-11.0	27440111
ECLASS-11.1	27440111
ECLASS-12.0	27440111
ECLASS-13.0	27440111
ECLASS-14.0	27440111
ETIM-5.0	EC002585
ETIM-6.0	EC002585
ETIM-7.0	EC002585
ETIM-8.0	EC002585
EAN	4048879300032
Electrical data Supply	
Total current max.	8 A
Installation	
Connection cross section max.	1.5 mm ²
AWG number max.	16
Installation Connection	
Connection	Spring clamp terminals FK
Device protection Media	
Flame resistance	flame retardant
Mechanical data Material data	
Material housing	Plastic
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	80 °C
Connection type 1	
Family construction form	Cap
No. of poles	21