

## **CAP BIG WITH PLUG. SPRING TERM. 21-POLE**

For use with 4-,6-,8-way d-box M12 5-pole

Art.No.: 8000-88549-0000000

Weight: 0.048 Country of origin: CZ

Model designation: MVZ12-HFK21H MVMX 21P. Cap for 4-, 6-, and 8-way distribution box, 5-pole

Spring clamp plug-in terminals


Plastic housings with good resistance against chemicals and oils.


The resistance to aggressive media should be individually tested for your application. Further details on request.

## **Link to Product**

## Illustration







Product may differ from Image



Header

Material short text

MVZ12-HFK21H MVMX 21P.

Commercial data



URL Webshop	https://shop.murrelektronik.com/8000-88549-0000000
GTIN	4048879300032
ECLASS-6.0	27143423
ECLASS-6.1	27279219
ECLASS-7.0	27279219
ECLASS-7.1	27279219
ECLASS-8.0	27279219
ECLASS-8.1	27279219
ECLASS-9.0	27440111
ECLASS-10.0.1	27440111
ECLASS-10.1	27440111
ECLASS-11.0	27440111
ECLASS-11.1	27440111
ECLASS-12.0	27440111
ECLASS-13.0	27440111
ECLASS-14.0	27440111
ETIM-5.0	EC002585
ETIM-6.0	EC002585
ETIM-7.0	EC002585
ETIM-8.0	EC002585
customs tariff number	85366990
EAN	4048879300032
Packaging unit	1
Electrical data   Supply	
Total current max.	8 A
Installation	
Connection cross section max.	1,5 mm²
AWG number max.	16
Installation   Connection	
Connection	Spring clamp terminals FK
Device protection   Media	
Flame resistance	flame retardant
Mechanical data   Material data	
Material housing	Plastic
Environmental characteristics   Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	80 °C
Connection type 1	
Family construction form	Сар
No. of poles	21