

**MODL. VARIO 10-way coupling housing type B**

nickel plated aluminum

Art.No.: M1850-100602

Weight: 0.257

Country of origin: DE

Model designation: EIS-Flansch body plug 10-fach\_lo

Mobile housing (round)

Aluminium

10-way

[\*\*Link to Product\*\*](#)**Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	27260702
ECLASS-6.1	27260708
ECLASS-7.0	27440312
ECLASS-8.0	27440312
ECLASS-9.0	27440312
ECLASS-10.1	27440312
ECLASS-11.1	27440312
ECLASS-12.0	27440312
ETIM-5.0	EC002641
customs tariff number	85389099
customs tariff number	85389099
GTIN	4048879573061
GTIN	4048879573061
Packaging unit	1
Packaging unit	1

**Device protection | Electrical**

Degree of protection (EN IEC 60529)	IP65, IP67, IP68
Degree of protection (ISO 20653:2013)	IP66K, IP69K
Additional condition protection degree	inserted, screwed

**Mechanical data**

Operating pressure min.	-0,8 bar
Operating pressure max.	16 bar

**Mechanical data | Material data**

Material housing	Aluminum die casting
Coating housing	powder-coated

**Mechanical data | Mounting data**

Mounting method	screw fixing
-----------------	--------------

**Environmental characteristics | Climatic**

Operating temperature min.	-20 °C
Operating temperature max.	120 °C