

MODL. VARIO 4-way coupling housing type B

stainless steel type 1.4404 (V4A)

Art.No.: M1851-040602

Weight: 0.369

Country of origin: DE

Model designation: EIS-Flansch body plug 4-fach_lo

Mobile housing

Stainless steel 1.4404 (V4A)

4-way

[Link to Product](#)**Illustration**

Product may differ from Image

Commercial data

ECLASS-6.0	27260702
ECLASS-6.1	27260708
ECLASS-7.0	27440312
ECLASS-8.0	27440312
ECLASS-9.0	27440312
ECLASS-10.1	27440312
ECLASS-11.1	27440312
ECLASS-12.0	27440312
ETIM-5.0	EC002641
customs tariff number	85389099
customs tariff number	85389099
GTIN	4048879573115
GTIN	4048879573115
Packaging unit	1
Packaging unit	1

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65, IP67, IP68
Degree of protection (ISO 20653:2013)	IP66K, IP69K
Additional condition protection degree	inserted, screwed

Mechanical data

Operating pressure min.	-0,8 bar
Operating pressure max.	16 bar

Mechanical data | Material data

Material housing	Stainless steel 1.4404 (V4A)
------------------	------------------------------

Mechanical data | Mounting data

Mounting method	screw fixing
-----------------	--------------

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
----------------------------	--------

Operating temperature max.	120 °C
----------------------------	--------