

Xelity 4TX Unmanaged Switch 4 Port 100Mbit

4 port unmanaged switch
Connection cables are in the online shop under "Connection Technology".

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	19170106
ECLASS-6.1	19170106
ECLASS-7.0	19170106
ECLASS-8.0	19170106
ECLASS-9.0	19170402
ECLASS-10.1	19170402
ECLASS-11.1	19170402
ECLASS-12.0	19170402
ETIM-5.0	EC000734
customs tariff number	85176200
GTIN	4048879785952
Packaging unit	1
Electrical data Supply	
Operating voltage DC min.	9,5 V
Operating voltage DC max.	31,5 V
Current consumption max.	35 mA
Industrial communication	
Data transmission rate max.	100 MBit/s
Industrial communication Ethernet functionality	
Auto-crossover	yes
Auto-negotiation	yes
duplex	Full duplex
Switch type	unmanaged

VLAN unmanaged (IEEE 802.1Q) yes

Diagnostics

Alarm contact no

Diagnostic No voltage

LED display Ethernet connection/data traffic

Device protection | Electrical

Degree of protection (EN IEC 60529) IP20

Invers-polarity protection yes

Over voltage protection yes

Mechanical data | Material data

Color housing black

Material housing Plastic

Mechanical data | Mounting data

Mounting method geschnappt

Suitable for mounting type Mounting rail TH35, (EN 60715)

Height 140 mm

Width 30 mm

Depth 85,1 mm

Environmental characteristics | Climatic

Operating temperature min. -25 °C

Operating temperature max. 60 °C

Storage temperature min. -40 °C

Storage temperature max. 85 °C

Connection type 2

Connection type 1 4

Family construction form RJ45

Gender female

Color contact carrier black

No. of poles 8

PIN 1 TD +

PIN 2 TD -

PIN 3 RD +

PIN 4 n.c.

PIN 5 n.c.

PIN 6 RD -

PIN 7 n.c.

PIN 8 n.c.

Connection Spring clamp terminals FK

Family construction form terminal

Gender female

Color contact carrier green

No. of poles 4

PIN 1 24 V DC (UB 1)

PIN 2 0 V

PIN 3 PE

PIN 4 n.c.