

**EUROCARD HOLDER**

SKP 32/D(A+C)

Screw terminals  
32-pole D (EN 60603)  
Row a, c

With the vertical snap adapter SASA 135 Art.-No. 63900 the holder can be mounted at right-angles on the rail.



The D2 size is for a card without a front plate.

Double row terminals on one side row for "a"

To insert the card first press down the 2 yellow buttons. Then slide the Eurocard into the guide slots pushing until fully engaged. The card is now locked into position. It can be removed by pressing down on the 2 yellow buttons.

**Link to Product**

**Illustration**



Product may differ from Image



**Commercial data**

ECLASS-6.0	27260710
ECLASS-6.1	27260704

ECLASS-7.0	27440402
ECLASS-8.0	27440402
ECLASS-9.0	27440402
ECLASS-10.1	27440402
ECLASS-11.1	27460201
ECLASS-12.0	27460201
ETIM-5.0	EC002780
customs tariff number	85366990
GTIN	4048879040075
Packaging unit	1

#### Electrical data | Supply

Operating voltage AC	250 V
Operating current max.	4 A

#### Installation

Connection cross-section solid max.	4 mm <sup>2</sup>
-------------------------------------	-------------------

#### Installation | Pin assignment

No. of poles	32
--------------	----

#### Device protection | Electrical

Overvoltage category (EN 60664-1)	I
-----------------------------------	---

#### Device protection | Media

Flame resistance	flame retardant
------------------	-----------------

#### Mechanical data

Type of socket connector	D (EN 60603)
--------------------------	--------------

#### Mechanical data | Material data

Material housing	Plastic
------------------	---------

#### Mechanical data | Mounting data

Mounting method	screwed, geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	137 mm
Width	63 mm
Depth	170 mm