

MODLINK MSDD SOCKET INSERT ITALY

250VAC/16A double

Italy (CEI 23-16)
with touch protection
Screw terminals

Link to Product

Illustration



Product may differ from Image



| Commercial data | |
|--|---------------|
| ECLASS-6.0 | 27189217 |
| ECLASS-6.1 | 27189217 |
| ECLASS-7.0 | 27189217 |
| ECLASS-8.0 | 27189217 |
| ECLASS-9.0 | 27182806 |
| ECLASS-10.1 | 27182806 |
| ECLASS-11.1 | 27182806 |
| ECLASS-12.0 | 27182806 |
| ETIM-5.0 | EC000020 |
| customs tariff number | 85366990 |
| GTIN | 4048879038232 |
| Packaging unit | 1 |
| Mechanical data Mounting data | |
| Height | 88 mm |
| Width | 51 mm |
| Depth | 33 mm |
| Environmental characteristics Climatic | |
| Storage temperature min. | -10 °C |
| Storage temperature max. | 60 °C |
| Italy (CEI 23-16) | |
| Connection cross section max. | 4 mm² |

| | |
|----------------------------|--------------------|
| AWG number max. | 12 |
| Operating voltage AC | 250 V |
| Operating current | 16 A |
| Connection | Screw terminals SK |
| No. of poles | 2 + PE |
| Connections per pole | 2 |
| Protection contact present | yes |