

MODLINK MSDD SOCKET INSERT SWITZERLAND

250VAC/10A

Swiss
Spring clamp terminals

Link to Product

Illustration



Product may differ from Image



Commercial data

ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC000020
customs tariff number	85366990
GTIN	4048879038188
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	30 mm

Environmental characteristics | Climatic

Storage temperature min.	-10 °C
Storage temperature max.	60 °C

Swiss

Connection cross section max.	1,5 mm²
AWG number max.	16

Operating voltage AC	250 V
Operating current	10 A
Connection	Spring clamp terminals FK
No. of poles	2 + PE
Connections per pole	2
Protection contact present	yes