

MODLINK MSDD DATA INSERT

1×USB-A fem./fem.+1×RJ45 fem./fem.+1×DVI fem./fem.

RJ45; USB (A); DVI
1× RJ45, 8-pole metal, CAT5e (female/female)
1× USB 2.0 (female/female) form A
1× DVI (female/female)

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data

ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27189217
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC002625
customs tariff number	85366990
GTIN	4048879037853
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	45 mm

Environmental characteristics | Climatic

Storage temperature min.	-10 °C
Storage temperature max.	60 °C

USB

Operating voltage AC	48 V
Operating voltage DC	48 V
Operating voltage DC (UL-listed)	42,4 V
Operating current max.	500 mA
USB specification	2.0
Data transmission rate max.	480 MBit/s
Looking techniques	Snap-in connector

RJ45

Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA
Family construction form	RJ45
Family type Back side	RJ45
Cable category min.	Cat5e
Looking techniques	Snap-in connector

DVI

Operating voltage AC max.	40 V
Operating current max.	1,5 A
Family type Back side	DVI
Gender	female
Gender Rear	female
No. of poles	24 + 4