

MODLINK MSDD DATA INSERT

1×SUB-D9 female/female + 1×RJ45 + 1×RJ12 + 1×USB-A

RJ45; RJ12; USB; USB (A); SUB-D9

1× RJ45, 8-pole metal, CAT5e (female/female)

1× RJ12 (6-pole plastic)

1× USB 2.0 (female/female) form A

1× SUB-D9 (female/female)

Link to Product

Illustration



Product may differ from Image

General data

Dimensions H×W×D 88×51×45 mm

RJ45

Operating current (UL Rating)	max. 175 mA
Locking of ports	Snap In
Connection front side	RJ45
Connection rear side	RJ45
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Specification	CAT5e, Class D, 100 MHz, (EN 50173-1)

SUB-D9

Connection rear side	SUB-D (female)
Operating current (UL Rating)	max. 175 mA
Connection front side	SUB-D (female)
Locking of ports	UNC 4...40 bolt
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current	3 A
No. of poles	9-pole
Operating voltage	48 V AC/DC

RJ12

Operating voltage	max. 48 V AC/DC
Connection front side	RJ12
Connection rear side	RJ12
Locking of ports	Snap In
Operating current	max. 1 A

Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current (UL Rating)	max. 175 mA

USB

Operating current	max. 500 mA
Specification	USB: 2.0 (max. 480 Mbit/s)
Locking of ports	Snap In
Operating voltage	48 V AC/DC
Operating voltage (UL Rating)	42.4 V DC

Shielding plate

Tightening torque	0.9 Nm \pm 0.1
Connection	Threaded hole M4

Article No.	4000-68000-1270000
-------------	--------------------