

MODLINK MSDD DATA INSERT

1×SUB-D9 male/male + 1×RJ45 + 2×PS2 fem./soldering

RJ45; SUB-D9; PS2; PS2
1 × RJ45, 8-pole metal, CAT5e (female/female)
1 × SUB-D9 (male/male)
2 × PS2 (6-pole solder connection)

Link to Product

Illustration



Product may differ from Image



Commercial data

ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC002625
customs tariff number	85366990
GTIN	4048879037464
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	21 mm

Environmental characteristics | Climatic

Storage temperature min.	5 °C
Storage temperature max.	40 °C

SUB-D9

Operating voltage AC	48 V
Operating voltage DC	48 V
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Operating current	3 A
Current operating max. (UL)	175 mA
Family construction form	SUB-D9
Family type Back side	SUB-D9
Gender	male
Gender Rear	male
Looking techniques	Standard UNC 4-40 screw thread bolt (EN 60807)
No. of poles	9

RJ45

Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA
Family construction form	RJ45
Family type Back side	RJ45
Cable category min.	Cat5e
Looking techniques	Snap-in connector

PS2

Connection cross section max.	0,5 mm ²
AWG number max.	20
Operating voltage AC	30 V
Operating voltage DC	30 V
Operating current	1 A
Family construction form	PS2
Family type Back side	PS2
Gender	female
Gender Rear	Lötanschluss
Looking techniques	Screw locking
No. of poles	6