

MODLINK MSDD SOCKET INSERT USA 2XNEMA 5-15

GFCI 125VAC/15A

USA (2× NEMA-GFCI 5-15)
(Ground Fault Circuit Interrupter)
Screw terminals

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC000020
customs tariff number	85366990
GTIN	4048879037280
Packaging unit	1
Mechanical data Mounting data	
Height	88 mm
Width	51 mm
Depth	27 mm
Environmental characteristics Climatic	
Storage temperature min.	-40 °C
Storage temperature max.	70 °C
USA	
Connection cross section max.	6 mm²

AWG number max.	10
Operating voltage AC	125 V
Operating current	15 A
Connection	Screw terminals SK
No. of poles	2 + PE
Connections per pole	2
Protection contact present	yes