

MODLINK MSDD SOCKET INSERT CHINA

250VAC/10A screw connection

China (CCC)
Screw terminals
with touch protection

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC000020
customs tariff number	85366990
GTIN	4048879037266
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	25 mm

Environmental characteristics | Climatic

Storage temperature min.	-30 °C
Storage temperature max.	60 °C

China (CCC)

Connection cross-section solid max.	4 mm ²
-------------------------------------	-------------------

Connection cross-section stranded/fine-stranded max.	4 mm²
Operating voltage AC	250 V
Operating current	10 A
Connection	Screw terminals SK
No. of poles	2 + PE
Connections per pole	2
Protection contact present	yes