

MODLINK MSDD DBL COMBI INSERT USA 2XNEMA 5-15

GFCI+2xRJ45 female/female + 1x3A fuse

- 2× NEMA-GFCI 5-15 (screw terminals)
- 2× RJ45, 8-pole metal, CAT5e (female/female)
- 1× fuse (3 A)
- with touch protection

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC000020
customs tariff number	85366990
GTIN	4048879369275
Packaging unit	1
Mechanical data   Mounting data	
Height	88 mm
Width	116 mm
Depth	72 mm
Environmental characteristics   Climatic	
Storage temperature min.	-40 °C
Storage temperature max.	70 °C
Fuse	

Operating voltage AC	250 V
----------------------	-------

Operating voltage DC	32 V
----------------------	------

Nominal current	3 A
-----------------	-----

**USA**

Connection cross section max.	6 mm <sup>2</sup>
-------------------------------	-------------------

AWG number max.	10
-----------------	----

Operating voltage AC	125 V
----------------------	-------

Operating current	15 A
-------------------	------

Connection	Screw terminals SK
------------	--------------------

No. of poles	2 + PE
--------------	--------

Connections per pole	2
----------------------	---

Protection contact present	yes
----------------------------	-----

**RJ45**

Operating voltage AC max. (UL-listed)	30 V
---------------------------------------	------

Operating voltage DC max. (UL-listed)	42,4 V
---------------------------------------	--------

Current operating max. (UL)	175 mA
-----------------------------	--------

Family construction form	RJ45
--------------------------	------

Family type Back side	RJ45
-----------------------	------

Cable category min.	Cat5e
---------------------	-------

Looking techniques	Snap-in connector
--------------------	-------------------