

T-Coupler M12 male/ M12 male w.cable+female A-cod.

4-pol. / 4-pol. + 8-pol.

AIDA conform

T-coupler (Slim Line)

Male straight – female/male straight

M12 – M12, 4-pole

Connection cable 0.2 m

Distribution function (NO)

for emergency-stop button (8-pole)

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**

Product may differ from Image

Technical Data

Operating voltage max. 30 V AC/DC

General data

Temperature range -25...+85 °C