

GBIT module - female, crimp t.


Female
Gigabit
Technical data will be only guaranteed with Murrelektronik components.
The clip 70MH-ZZ100-0000000 is needed (2×)

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27143424
ECLASS-6.1	27261204
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796
customs tariff number	85389099
GTIN	4048879664011
Packaging unit	1
Electrical data Supply	
Operating voltage AC	50 V
Operating voltage DC	50 V
Operating current	5 A
Industrial communication	
Transfer parameters	CAT6A
Installation	
Connection cross section min.	0,08 mm²
Connection cross section max.	0,5 mm²

AWG number min.	28
-----------------	----

AWG number max.	20
-----------------	----

Installation | Connection

Stripping length	4,2 mm
------------------	--------

Wire insulation diameter min.	5 mm
-------------------------------	------

Wire insulation diameter max.	7 mm
-------------------------------	------

Connection	Crimp
------------	-------

Gender	female
--------	--------

Mating cycles min.	500
--------------------	-----

Installation | Pin assignment

No. of poles	8
--------------	---

Device protection | Electrical

Pollution Degree	3
------------------	---

Rated surge voltage	0,8 kV
---------------------	--------

Overvoltage category (EN 60950-1)	III
-----------------------------------	-----

Mechanical data | Material data

Combustibility class (UL94)	V-0
-----------------------------	-----

Material housing	PC
------------------	----

Mechanical data | Mounting data

Number of module slots	1
------------------------	---

Height	50,4 mm
--------	---------

Width	34,1 mm
-------	---------

Depth	14,6 mm
-------	---------

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
----------------------------	--------

Operating temperature max.	85 °C
----------------------------	-------