

2,5 mm crimp contact m/turned/silver/2,5 mm²

100 pieces

Turned crimp contact  
Male  
2.5 mm  
2.5 mm² (AWG 14)  
Quantity: 100 pcs.  
Technical data will be only guaranteed with Murrelektronik components.

Link to Product

Illustration



Product may differ from Image

Commercial data	
ECLASS-6.0	27143424
ECLASS-6.1	27261202
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796
customs tariff number	85366990
GTIN	4048879650199
Packaging unit	100
Installation	
Connection cross section max.	2,5 mm²
AWG number max.	14
Installation   Connection	
Stripping length	6,5 mm
Connection	Crimp
Gender	male
Mating cycles min.	500
Mechanical data   Material data	
Coating contact	silver-plated

Brass

Height	4,5 mm
Width	4,5 mm
Depth	25 mm

---

Depth 25 mm