

**1,6 mm crimp contact f/turned/gold/0,14-0,37 mm<sup>2</sup>**

100 pieces

Turned crimp contact

Female

1.6 mm

0.14...0.37 mm<sup>2</sup> (AWG 26...22)

Quantity: 100 pcs.

Technical data will be only guaranteed with Murrelektronik components.

**[Link to Product](#)****Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	27143424
ECLASS-6.1	27261202
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796
customs tariff number	85366990
GTIN	4048879653565
Packaging unit	100

**Installation**

Connection cross section min.	0,14 mm <sup>2</sup>
Connection cross section max.	0,37 mm <sup>2</sup>
AWG number min.	26
AWG number max.	22

**Installation | Connection**

Stripping length	7 mm
Connection	Crimp
Gender	female
Mating cycles min.	500

**Mechanical data | Material data**

Coating contact	gold plated
Material contact	Brass
<b>Mechanical data   Mounting data</b>	
Height	3,5 mm
Width	3,5 mm
Depth	21,6 mm